



5035

## Series push-button 2 NO contacts with common input terminal

### Technical characteristics

#### Architecture

Type of control unit double rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode 2 NO, common input terminal

Antibacterial treatment No

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 41.6 mm

Insertion depth 32.3 mm

Height 70.8 mm

Width 70.8 mm

#### Materials

Material Plastic/metal

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

#### Scope of delivery

With lamp No

#### Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1
Lighting	for illumination
<b>Use cases</b>	
Application	Light control
<b>Safety</b>	
Protection index IP	IP20
<b>Identification</b>	
Application, usage	Light control
Main design line	Light control
<b>Instructions</b>	
Information text	spreader claws, insulated to the supporting ring, self-resetting