



5035

Series push-button 2 NO contacts with common input terminal

Technical characteristics

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode 2 NO, common input terminal

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 32.3 mm

Height 70.8 mm

Width 70.8 mm

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts 1

Quantity of NO contacts 1

Lighting for illumination

Use cases

Application	Light control
-------------	---------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	Yes
--------------	-----

Identification

Application, usage	Light control
--------------------	---------------

Main design line	Light control
------------------	---------------

Instructions

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--