



503503

Double mom. Cont. Switch

Technical characteristics

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode 2 NO contacts, separate input terminals

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 31.7 mm

Height 71 mm

Width 71 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts	1
Quantity of NO contacts	1
Lighting	can be illuminated using neon lamp, incandescent or LED unit with N terminal, for lighting and monitoring circuit
Use cases	
Application	Light control
Safety	
Protection index IP	IP20
Identification	
Application, usage	Light control
Main design line	Light control
Instructions	
Information text	spreader claws, insulated to the supporting ring, self-resetting