



53420216

Soc.out. insert earth. contact BRIT.ST.,can be switched off,enhncd contact prot.

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	13 A

Cover, door

Cover	Central cover plate
-------	---------------------

Materials

Colour independent of design lines	anthracite
Colour	anthracite

Installation, mounting

Installation mode	without spreader claws ; for screw fastening
-------------------	--

Connection

Connection terminals	according to IEC 60884-1
----------------------	--------------------------

Use

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	with screw terminals

Safety

IK protection code against mechanical impacts	IK02
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
------------------	------------------------