



459410

Aerial soc. 4hole single box, DC-permeable, 1930/glass/R.classic

Technical characteristics

Functions

Function Suitable for HDTV

Connectivity

Connectors / jacks remote supply via F-sockets

Outputs with 2 independent SAT outputs (F-sleeves) and 2 IEC outputs (male/female)

Reception / transmission for terrestrial reception ; for digital and analogue transmission

Voltage

Voltage DC voltage conducting

Frequency

Broadband technology 5...2400 MHz

Resistance

Wave impedance 75 Ω

Attenuation

Tap loss at 2150 MHz 2 dB

Tap loss at 860 MHz 2 dB

Installation, mounting

System for community and broadband cable systems ; for single and distributor SAT systems ; for multi-switch systems

Connection

Type of connection with screw terminals

Connection for simultaneous connection of radio and TV receiver as well as 2 independent SAT receivers

Settings

Programs also to add SAT programmes in broadband cable systems

Equipment

Supporting plate / Supporting ring external eyelets on the supporting ring can be broken off for round designs

Use

Differentiation characteristic 3 - Sales DC-permeable

Standards

Safety

Protective screen	(VHF/UHF) according to EN 50083-2, Class B ; (SAT) according to EN 50083-2, Class A
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-25...55 °C
-----------------------	-------------

Identification

Application, usage	Communication technology
Main design line	Communication technology