



459410

**Aerial soc. 4hole single box, DC-permeable, 1930/glass/R.classic**

**Technical characteristics**

**Functions**

Function Suitable for HDTV

**Connectivity**

Connectors / jacks remote supply via F-sockets

Outputs with 2 independent SAT outputs (F-sleeves) and 2 IEC outputs (male/female)

Reception / transmission for terrestrial reception, for digital and analogue transmission

**Voltage**

Voltage DC voltage conducting

**Frequency**

Broadband technology 5...2400 MHz

**Resistance**

Wave impedance 75 Ω

**Attenuation**

Tap loss at 2150 MHz 2 dB

Tap loss at 860 MHz 2 dB

**Materials**

Material metal

**Installation, mounting**

System for community and broadband cable systems, for single and distributor SAT systems, for multi-switch systems

**Connection**

Type of connection with screw terminals

Connection for simultaneous connection of radio and TV receiver as well as 2 independent SAT receivers

**Settings**

Programs also to add SAT programmes in broadband cable systems

**Equipment**

Supporting plate / Supporting ring external eyelets on the supporting ring can be broken off for round designs

**Use**

**Standards**

General standards

EN 50083-2 and EN 60728-4

**Safety**

Protective screen

(VHF/UHF) according to EN 50083-2, Class B, (SAT)  
according to EN 50083-2, Class A

Protection index IP

IP20

**Use conditions**

Operating temperature

-25...55 °C

**Identification**

Application, usage

Communication technology

Main design line

Communication technology