



6765096014

Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,Q.x,orange velv

Technical characteristics

Architecture

Number of poles 2pole + earth

Configuration

Number of modules 1

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Frequency 50/60 Hz

Rated current 16 A

Dimensions

Insertion depth 32 mm

Cover, door

Cover Central cover plate

Materials

Design lines special colours orange

Surface appearance velvety

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60884-1

Type of connection with screw-in lift terminals

Use

Differentiation characteristic 2 - Sales with enhanced touch protection

Differentiation characteristic 3 - Sales Screw-in lift terminals

Safety

REACH conform Yes

RoHS conform Yes

Halogen free No

Protection Enhanced contact protection

With enhanced contact protection Yes

Identification

