



47087004

**SCHUKO soc.out. residual current circuit-breaker,enhncd contact prot.,K5,steel,**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Type	type A for alternating currents and pulsating direct currents

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Measurement error current	30 mA
Rated current	16 A
Surge current resistance	250 A (8/20) $\mu$ s
Short-circuit resistance (with back-up fuse 20 AgL)	3 kA

**Dimensions**

Insertion depth	31.9 mm
-----------------	---------

**Tripping**

Trigger time	$\leq$ 30 ms
--------------	--------------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	stainless steel
Material / workmanship	lacquered
Surface appearance	matt

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Use cases**

---

Application	Security and safety systems
-------------	-----------------------------

**Use**

---

Differentiation characteristic 2 - Sales	enhanced contact protection
------------------------------------------	-----------------------------

**Standards**

---

Tested	conform VDE 0664 (EN 61008)
--------	-----------------------------

**Safety**

---

IK protection code against mechanical impacts	07
-----------------------------------------------	----

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	No
--------------	----

---

Protection	Enhanced contact protection
------------	-----------------------------

---

With enhanced contact protection	Yes
----------------------------------	-----

**Identification**

---

Main design line	Berker K.5
------------------	------------