



47232089

**SCHUKO soc. out., enhncd contact prot., R.1/R.3, p. white glossy**

**Technical characteristics**

**Architecture**

Design	according to DIN 49440
Fixing mode	flush-mounting

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Electric current**

Rated current	16 A
---------------	------

**Dimensions**

Insertion depth	32 mm
Installation depth, flush-mounted boxes	31 mm

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	polar white
Colour	polarwhite
Colour	white
RAL colour	RAL 9010 - Pure white
Material	thermoplastic
Material for printing	ASA polar white
Metallic colour	No

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Connection terminals	according to VDE 0620-1
Type of connection	with plug-in terminals

**Settings**

---

Shading parameter	R1_biały
Laser parameter	R1_weiß

---

**Equipment**

---

Type of configuration	Laserdruck
-----------------------	------------

---

**Use**

---

Differentiation characteristic 2 - Sales	with enhanced touch protection
--	--------------------------------

---

**Safety**

---

Protection index IP	IP20
---------------------	------

---

Protection	Enhanced contact protection
------------	-----------------------------

---

With enhanced contact protection	Yes
----------------------------------	-----

---

**Identification**

---

Main design line	Berker R.1/R.3/R.8
------------------	--------------------

---

Secondary design line(s)	Berker R.1, Berker R.3, Berker R.8
--------------------------	------------------------------------