



75141326



IP20



Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions
Light scenes	retrieval, adjustment and storage of 8 light scenes

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	1
Operation	one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H)	56.4 mm
Height	71 mm
Width	71 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of labelling	217,217,217
Colour of design line	anthracite
Colour	anthracite
RAL colour	RAL 7021 - Black grey
Material	Plastic/metal
Material for printing	Paper
Surface appearance	velvety
Type of surface treatment	untreated
Material family	Plastic

LED control

LED	with white operation LED and 2 amber status LEDs
-----	--

Settings

Supported configuration modes	system
Parameterisation	single and two push-button operation parameterisable

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of actuation points	2
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 1gang
Controller extension unit	usable as thermostat extension unit

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	with integral bus coupling unit

Safety

Protection index IP	IP20
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX, Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text	Labelling field sheet, order no. 9498 29 01, available separately.
------------------	---