



75142326



IP20



## Technical characteristics

### Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Light scenes retrieval, adjustment and storage of 8 light scenes

### Compatibility

Extension unit extension unit for light scene push-button

### Controls and indicators

With LED indication Yes

Number of buttons 2

Operation one push-button operation for switching, pushing, shutters and dimming

### Dimensions

Labelling field length (W x H) 56.4 x 26.8 mm

Height 71 mm

Width 71 mm

### Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

### Screen

With display No

### Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Material for printing Paper

Surface appearance velvety

Material family Plastic

### LED control

LED with white operation LED and 4 amber status LEDs

### Settings

Supported configuration modes system

Parameterisation single and two push-button operation parameterisable

### Scope of delivery

Bus connection included Yes

### Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 2gang
Controller extension unit	usable as thermostat extension unit

### Use

Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with integral bus coupling unit

### Safety

Protection	with dismantling protection
------------	-----------------------------

### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

### Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

### Instructions

Information text	Labelling field sheet, order no. 9498 30 02, available separately.
------------------	--