



75143329

IP20



Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Light scenes retrieval, adjustment and storage of 8 light scenes

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 3

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 56.4 x 17 mm

Height 71 mm

Width 71 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of design line polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Material for printing Paper

Surface appearance velvety

Type of surface treatment untreated

Material family Plastic

LED control

LED with white operation LED and 6 amber status LEDs

Settings

Supported configuration modes	system
-------------------------------	--------

Parameterisation	single and two push-button operation parameterisable
------------------	---

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of actuation points	6
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Type of configuration	Beschriftungsfeld(er) - Folie
-----------------------	-------------------------------

Product type:	product type: push-button 3gang
---------------	---------------------------------

Controller extension unit	usable as thermostat extension unit
---------------------------	-------------------------------------

Use

Differentiation characteristic 1 - Sales	with labelling fields
--	-----------------------

Differentiation characteristic 3 - Sales	with integral bus coupling unit
--	---------------------------------

Safety

Protection index IP	IP20
---------------------	------

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Product family	product family: push-button
----------------	-----------------------------

Secondary design line(s)	KNX, Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9
--------------------------	---

Instructions

Information text	Labelling field sheet, order no. 9498 31 03, available separately.
------------------	---