



75162093



**IP20**

**B.IQ push-button 2gang, KNX - B.IQ, stainless steel, metal brushed**

**Technical characteristics**

**Functions**

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

**Compatibility**

Extension unit	extension unit for light scene push-button
----------------	--

**Controls and indicators**

With LED indication	Yes
Number of buttons	2

**Dimensions**

Depth	16.65 mm
Assembling height	16.7 mm
Height	88.5 mm
Width	88.5 mm

**Measurement**

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

**Screen**

With display	No
--------------	----

**Materials**

Colour of design line	Stainless steel
Material / workmanship	metal brushed
Surface appearance	matt
Material family	Metal

**LED control**

LED	with blue operation LED and 4 white status LEDs (labelling field illumination)
-----	--

**Connection**

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Accessories included**

Box	for installation in single standard wall boxes
-----	--

for stainless steel frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

---

**Equipment**

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

---

**Safety**

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

---

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

---

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ