



75162093

IP20

B.IQ push-button 2gang, KNX - B.IQ, stainless steel, metal brushed

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
----------------------------------	----

Function	for switch, push-button, dimmer and shutter functions
----------	---

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
---------------------	-----

Number of buttons	2
-------------------	---

Dimensions

Depth	16.65 mm
-------	----------

Assembling height	16.7 mm
-------------------	---------

Height	88.5 mm
--------	---------

Width	88.5 mm
-------	---------

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	Stainless steel
-----------------------	-----------------

Colour	stainless steel
--------	-----------------

RAL colour	RAL 9022 - Pearl light grey
------------	-----------------------------

Material / workmanship	metal brushed
------------------------	---------------

Material	stainless steel
----------	-----------------

Surface appearance	matt
--------------------	------

Type of surface treatment	brushed
---------------------------	---------

Material family	Metal
-----------------	-------

LED control

LED	with blue operation LED and 4 white status LEDs (labelling field illumination)
-----	--

Connection

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
Matching products	for stainless steel frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Equipment

Number of actuation points	4
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ