



75164094



IP20

B.IQ push-button 4gang, KNX - B.IQ, al., al. anodised

Technical characteristics

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Dimensions

Assembling height 16.7 mm

Height 118.1 mm

Width 88.5 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line Aluminium

Material / workmanship aluminium, anodised

Surface appearance matt

Material family Metal

LED control

LED with blue operation LED and 8 white status LEDs

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

Bus connection included No

Accessories included

Box for installation in single standard wall boxes

for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for aluminium frames in the same "style" for additional applications, see the Design line B.7

Matching products

Equipment

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Product type:	product type: B.IQ

Safety

REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ