


75168692



B.IQ push-button 4gang for light scenes, KNX - B.IQ, glass black

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	No
Light scenes	light scene push-buttons can be cascaded, retrieval, adjustment and storage of 8 light scenes

Controls and indicators

With LED indication	Yes
Number of buttons	4
Operation	second operating level for setting load groups via 3-button actuation

Dimensions

Assembling height	16.7 mm
Height	118.1 mm
Width	88.5 mm

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	glass black
Colour	black
RAL colour	RAL 9005 - Jet black
Material	glass
Type of surface treatment	Painted

LED control

LED	with blue operation LED and 8 white status LEDs (labelling field illumination)
-----	--

Connection

Number of load groups (increase on cascading)	8
Bus coupling unit	for bus coupling unit flush-mounted

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
	for glass frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x
Matching products	

Equipment

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Light scenes	max. 8
Product type:	product type: B.IQ

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ