



5031

## Rocker push-button NO contact Module insert

### Technical characteristics

#### Architecture

Type of control unit	rocker
----------------------	--------

#### Functions

Switching angle	3.5 °
-----------------	-------

#### Configuration

Switch mode	Normally open contact
-------------	-----------------------

#### Compatibility

IFTTT support available	No
-------------------------	----

#### Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz

#### Electric current

Momentary-contact current	10 A
---------------------------	------

#### Dimensions

Depth	41.6 mm
Insertion depth	30 mm
Contact spacing	> 3 mm
Height	70.8 mm
Width	70.8 mm

#### Materials

Material	Plastic/metal
----------	---------------

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Conductor cross-section (rigid)	2.5
Connection terminals	according to IEC 60669-1
Connection terminals	according to VDE 0632-1
Type of connection	with plug-in terminals

#### Scope of delivery

With lamp	No
-----------	----

<b>Equipment</b>	
Quantity of NC contacts	0
Quantity of NO contacts	1
Lighting	for lighting and monitoring circuit
<b>Use cases</b>	
Application	Barrier-free application, HVAC-control, Light control
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Identification</b>	
Application, usage	Light control
Main design line	Light control
<b>Instructions</b>	
Information text	spreader claws, insulated to the supporting ring, self-resetting