



75261585

**KNX cont. comf 1.1 m, KNX - B.3/B.7, ant., matt**

#### Technical characteristics

##### Architecture

Fixing mode	flush-mounting
-------------	----------------

##### Functions

Max. temporisation	306 h
--------------------	-------

Potentiometer for additional delay time	± 50 %
---	--------

Lockout time	8 ms...140 mn
--------------	---------------

Function	Functions for lighting operating mode: Switching, Value transmitter and Light scene call, parameter defineable lock function
----------	--

Slide switch	with slide switch for OFF/automatic/ON
--------------	--

##### Compatibility

Extension unit	also suitable as extension unit
----------------	---------------------------------

##### Controls and indicators

Number of switching segments	72
------------------------------	----

##### Dimensions

Dimensions assembling height	23.5 mm
------------------------------	---------

Nominal mounting height	1.1 m
-------------------------	-------

Optimum mounting height	1.1 m
-------------------------	-------

##### Power

Power consumption, KNX	≈ 110 mW
------------------------	----------

##### Measurement

Detection field, semi-oval shaped	≈ 10 x 12 m
-----------------------------------	-------------

##### Reach distance

Range, frontal	≈ 10 m
----------------	--------

Range, side	each ≈ 6 m
-------------	------------

Max. transmission range frontally	10 m
-----------------------------------	------

Max. transmission range sideways	6 m
----------------------------------	-----

##### Cover, door

Cover	with cover to limit detection angle to 90°
-------	--

##### Detection

Number of detection levels	2
----------------------------	---

Detection angle	180 °
-----------------	-------

Detection angle vertical	0 / 7 °
--------------------------	---------

Detection angle horizontal	0 / 180 °
Sensor type	detector of movement
<b>Materials</b>	
Colour of design line	anthracite
RAL colour	RAL 7021 - Black grey
Material	thermoplastic
Surface appearance	matt
<b>Lighting control</b>	
Response brightness, configurable	3...100 lx / daytime operation
<b>LED control</b>	
LED	with red diagnostic LED for brightness-independent walk test function and disassembly message
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	0 W
<b>Connection</b>	
Bus coupling unit	for bus coupling unit flush-mounted
<b>Settings</b>	
Supported configuration modes	system
Response brightness adjustable by potentiometer	± 50 %
Response sensitivity, settable	20...100 %
Min. temporisation	130 ms
Delay time	≈ 10 s
Additional delay time programmable	130 ms...306 h
Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time
<b>Equipment</b>	
Product type:	product type: movement
Lighting	with lighting and message mode
<b>Safety</b>	
Alarm	alarm telegram after disconnection from bus coupling unit, 1-bit
<b>Use conditions</b>	
Operating temperature	-5...45 °C
<b>Identification</b>	
Application, usage	KNX - sensors
Product family	product family: physical sensors
Main design line	KNX - Berker B.3/B.7
Secondary design line(s)	KNX, Berker B.7, Berker B.3, Motion detector, Berker B.1
<b>Instructions</b>	

Information text

Caution: Direct sunlight can lead to false alarms when using alarm application. Avoid using detection field equipment on windows. Continuous direct sunlight penetrating the upward-pointing detection level can result in failure of the controller. Only suitable for indoor areas!