



503101

Push-button NO contact with two signal contacts

Technical characteristics

Architecture

Type of control unit rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode NO, with 2 separate signalling contacts

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Connection

Conductor cross-section (rigid) 2.5

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Scope of delivery

With lamp No

Equipment

Quantity of NC contacts 0

Quantity of NO contacts

1

Lighting

for lighting and monitoring circuit

Use cases

Application

Barrier-free application, HVAC-control, Light control

Safety

Protection index IP

IP20

Identification

Application, usage

Light control

Main design line

Light control

Instructions

Information text

spreader claws, insulated to the supporting ring, self-resetting