



503101

## Push-button NO contact with two signal contacts

### Technical characteristics

#### Architecture

Type of control unit rocker

#### Functions

Switching angle 3.5 °

#### Configuration

Switch mode NO, with 2 separate signalling contacts

#### Compatibility

IFTTT support available No

#### Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

#### Electric current

Momentary-contact current 10 A

#### Dimensions

Depth 41.6 mm

Insertion depth 31 mm

Height 71 mm

Width 71 mm

#### Installation, mounting

Installation mode with spreader claws

#### Connection

Conductor cross-section (rigid) max. 2.5 mm<sup>2</sup>

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

#### Scope of delivery

With lamp No

#### Equipment

Quantity of NC contacts 0

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

**Use cases**

---

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

**Safety**

---

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

**Identification**

---

Application, usage	Light control
Main design line	Light control

**Instructions**

---

Information text	spreader claws, insulated to the supporting ring, self-resetting
------------------	--