



503150

**Push-button, NO contact for installation in hollow walls, Module inserts**

**Technical characteristics**

**Architecture**

Type of control unit rocker

**Functions**

Switching angle 3.5 °

**Configuration**

Switch mode Normally open contact

Antibacterial treatment No

**Compatibility**

IFTTT support available No

**Main electrical features**

Nominal voltage 250 V

Rated voltage 250 V AC

**Electric current**

Momentary-contact current 10 A

**Dimensions**

Depth 41.6 mm

Insertion depth 19.5 mm

Height 71 mm

Width 71 mm

**Installation, mounting**

Installation mode low installation depth ; without spreader claws ; for screw fastening

**Connection**

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

**Scope of delivery**

With lamp No

**Equipment**

Quantity of NC contacts 0

Quantity of NO contacts 1

Lighting for lighting and monitoring circuit

**Use cases**

---

Application	Barrier-free application ; HVAC-control ; Light control
-------------	---

**Safety**

---

REACH conform	No
RoHS conform	Yes
Halogen free	Yes

**Identification**

---

Application, usage	HVAC control ; Light control
Main design line	Light control