



503501

Series push-button NC contact and NO contacts with isolated input terminals

Technical characteristics

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode 1 NO, 1 NC, separate input terminals

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 31.3 mm

Height 71 mm

Width 71 mm

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting can be illuminated using neon lamp, incandescent or LED unit with N terminal ; for lighting and monitoring circuit

Use cases

Application Light control

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |
| Halogen free | Yes |

Identification

| | |
|--------------------|---------------|
| Application, usage | Light control |
| Main design line | Light control |

Instructions

| | |
|------------------|--|
| Information text | spreader claws, insulated to the supporting ring, self-resetting |
|------------------|--|
