



503501

Series push-button NC contact and NO contacts with isolated input terminals

Technical characteristics

Architecture

Type of control unit double rocker

Functions

Switching angle 3.5 °

Configuration

Switch mode 1 NO, 1 NC, separate input terminals

Antibacterial treatment No

Compatibility

IFTTT support available No

Main electrical features

Nominal voltage 250 V

Rated voltage 250 V AC

Electric current

Momentary-contact current 10 A

Dimensions

Depth 41.6 mm

Insertion depth 31.3 mm

Height 71 mm

Width 71 mm

Materials

Material Plastic/metal

Installation, mounting

Installation mode with spreader claws

Connection

Connection terminals according to IEC 60669-1

Connection terminals according to VDE 0632-1

Type of connection with plug-in terminals

Type of connection Quickconnect

Equipment

Lighting can be illuminated using neon lamp, incandescent or LED unit with N terminal ; for lighting and monitoring circuit

Use cases

Application

Light control

Safety

Protection index IP

IP20

Identification

Application, usage

Light control

Main design line

Light control

Instructions

Information text

spreader claws, insulated to the supporting ring, self-resetting