



75662775



Push-button 2gang with room thermostat, display, K.1, anthracite

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller Yes

Timers with room temperature timer

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 2

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 66.8 x 15.7 mm

Height 55.1 mm

Width 70.9 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display Yes

Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Colour anthracite

RAL colour RAL 7021 - Black grey

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

Material family Plastic

LED control

LED with white operation LED and 4 red status LEDs

Connection

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	---

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
-----	--

Equipment

Number of actuation points	6
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 2gang
Control	for individual single room temperature control

Software

Update	with flash-controller technology
--------	----------------------------------

Safety

Protection index IP	IP20
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

Use conditions

Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker K.1/K.5
Secondary design line(s)	KNX, Berker K.1