



75663593



## B.IQ push-b. 3gang thermostat, display, KNX - B.IQ, stainl. steel metal brushed

### Technical characteristics

#### Functions

With room temperature controller	Yes
Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming

#### Dimensions

Width of rail mounted device (RMD)	0 modules
Height	119.6 mm
Width	88.5 mm

#### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

#### Materials

Colour of design line	Stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	metal brushed
Material	stainless steel
Material family	Metal

#### LED control

LED	with blue operation LED and 6 white status LEDs (labelling field illumination)
-----	--

#### Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

#### Accessories included

Box	for installation in single standard wall boxes
-----	--

for stainless steel frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Matching products

---

**Equipment**

Product type: product type: B.IQ

Control for individual single room temperature control

---

**Software**

Update with flash-controller technology

---

**Safety**

Protection with dismantling protection

---

**Use conditions**

Operating temperature -5...45 °C

Energy efficiency class IV (2%)

---

**Identification**

Application, usage KNX - operating systems

Product family product family: push-button

Release issue 2.6

Main design line KNX - Berker B.IQ

Secondary design line(s) KNX, Berker B.IQ