



75663773



## Push-button 3gang with room thermostat, display, K.5, stainless steel

### Technical characteristics

#### Functions

With room temperature controller	Yes
Function	with valve protection function ; for switch, push-button, dimmer, blind and thermostat functions
Timers	with room temperature timer
Operating mode	controller operating modes: comfort, standby, night and frost/heat protection mode

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Dimming	area dimming
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming ; blind operating concepts short-long-short and long-short parameterisable
Indication / display	LC display with symbol display ; display of operating mode, controller lockout, room/outside temperature, time (clock required)
Button / push-button	with 2 additional display buttons

#### Connectivity

Encoding	with button blocking function
----------	-------------------------------

#### Dimensions

Labelling field length (W x H)	66.8 x 24.9 mm
Height	111.1 mm
Width	70.9 mm

#### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

#### Screen

With display	Yes
--------------	-----

#### Materials

Colour of labelling	105,105,105
Colour of design line	stainless steel
Material for printing	Paper
Surface appearance	matt

**LED control**

LED	with white operation LED and 6 red status LEDs
-----	--

**Connection**

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

**Settings**

Parameterisation	single and two push-button operation parameterisable ; presence button parameterisable to extend comfort ; end customer display scope parameterisable
Programming	programmable from ETS2, V1.2a

**Scope of delivery**

Bus connection included	No
-------------------------	----

**Equipment**

Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang
Heating	for heating and/or cooling mode with/without auxiliary step
Control	for continuous (PI) or switched (2-point) control of max. 2 control circuits ; control parameter for heating / cooling unit pre-set ; for individual single room temperature control

**Use**

Differentiation characteristic 1 - Sales	Labelling fields
Differentiation characteristic 2 - Sales	Display

**Software**

Update	with flash-controller technology
--------	----------------------------------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte

**Use conditions**

Operating temperature	-5...45 °C
Temperature	temperature measurement via internal and/or external sensor with mean value formation
Energy efficiency class	IV (2%)

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button

Main design line

KNX - Berker K.1/K.5

Secondary design line(s)

KNX ; Berker K.5

---

**Instructions**

Special note text

Use only in combination with frame frame with large cut-out.