



6765096086

**Soc.out. earth.pin+LED,enhncd contact prot.,screw-in lift term.,Q.x,ant.velv**

**Technical characteristics**

**Architecture**

Fixing mode	flush-mounting
Number of poles	2pole + earth

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

**Dimensions**

Insertion depth	32 mm
-----------------	-------

**Cover, door**

Cover	Central cover plate
-------	---------------------

**Materials**

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	duroplastic
Surface appearance	velvety

**Installation, mounting**

Installation mode	with spreader claws
-------------------	---------------------

**Connection**

Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

**Use**

Differentiation characteristic 2 - Sales	with enhanced touch protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

**Safety**

Protection	Enhanced contact protection
------------	-----------------------------

**Identification**

---

Main design line

Berker Q.1/Q.3/Q.7/Q.9

---

Secondary design line(s)

Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9