



75663780



S.1/B.3/B.7 Push Button 3-gang, with Thermostat/Label, White/Polar White

Technical characteristics

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With room temperature controller	Yes
Function	for switch, push-button, dimmer, blind and thermostat functions, with valve protection function
Timers	with room temperature timer
Operating mode	controller operating modes: comfort, standby, night and frost/heat protection mode

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Dimming	area dimming
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming, blind operating concepts short-long-short and long-short parameterisable
Indication / display	display of operating mode, controller lockout, room/outside temperature, time (clock required), LC display with symbol display
Button / push-button	with 2 additional display buttons

Connectivity

Encoding	with button blocking function
----------	-------------------------------

Dimensions

Labelling field length (W x H)	52.3 x 24.9 mm
Height	110.8 mm
Width	55.8 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	Yes
--------------	-----

Materials

Colour independent of design lines	for white and polar white
Colour	other

RAL colour	RAL 1013 - Oyster white
Material	thermoplastic
Material for printing	Paper
Type of surface treatment	untreated
LED control	
LED	with white operation LED and 6 red status LEDs
Connection	
Bus coupling unit	for bus coupling unit flush-mounted
Settings	
Parameterisation	end customer display scope parameterisable, single and two push-button operation parameterisable, presence button parameterisable to extend comfort
Programming	programmable from ETS2, V1.2a
Scope of delivery	
Bus connection included	No
Equipment	
Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang
Heating	for heating and/or cooling mode with/without auxiliary step
Control	for individual single room temperature control, control parameter for heating / cooling unit pre-set, for continuous (PI) or switched (2-point) control of max. 2 control circuits
Use	
Differentiation characteristic 1 - Sales	Labelling fields
Differentiation characteristic 2 - Sales	Display
Software	
Update	with flash-controller technology
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte
Use conditions	
Operating temperature	-5...45 °C
Temperature	temperature measurement via internal and/or external sensor with mean value formation
Energy efficiency class	IV (2%)

Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker S.1/B.3/B.7
Secondary design line(s)	KNX, Berker S.1, Berker B.3, Berker B.7
Instructions	
Special note text	Use only in combination with frame frame with large cut-out.