



6765106086

Soc.out. earth.pin+LED orient.,enhncd contact prot.,screw-in lift ,Q1/3,ant.velv

Technical characteristics

Architecture

Fixing mode	flush-mounting
Number of poles	2pole + earth

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Rated voltage	250 V AC
Frequency	50/60 Hz
Rated current	16 A

Power

Power consumption	0.25 W/0.35 VA
-------------------	----------------

Cover, door

Cover	Central cover plate
-------	---------------------

Detection

Sensor	integrated brightness sensor that switches the orientation light on at twilight and off when there is sufficient brightness
--------	---

Materials

Colour of design line	anthracite
Colour	anthracite
Colour	anthracite charcoal grey
RAL colour	RAL 7021 - Black grey
Material / workmanship	lacquered
Material	thermoplastic
Surface appearance	velvety

Lighting control

Switch-off brightness	4 lx
Switch-on brightness	2 lx
Light intensity (white)	0.2 cd

LED control

LED	long service life of the LED, white LED light
-----	---

Installation, mounting

Connection

Conductor cross-section (rigid)	2.5
Connection terminals	according to IEC 60884-1
Type of connection	with screw-in lift terminals

Cable

Wiring	through-wiring possible, therefore also ideal for retrofitting
--------	--

Equipment

Lighting	additional benefit by combination of a socket outlet with an orientation light
----------	--

Use

Differentiation characteristic 2 - Sales	enhanced contact protection
Differentiation characteristic 3 - Sales	Screw-in lift terminals

Safety

IK protection code against mechanical impacts	05
Protection	Enhanced contact protection
With enhanced contact protection	Yes

Identification

Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1, Berker Q.3, Berker Q.7, Berker Q.9

Instructions

Information text	Caution! Items with special flush-mounted insert. Centre plates with LED orientation lights are not compatible with the standard socket outlets.
------------------	--