



75664594



B.IQ push-button 4gang thermostat, display, KNX - B.IQ, al., al. anodised

Technical characteristics

Functions

| | |
|----------------------------------|--|
| With room temperature controller | Yes |
| Function | for switch, push-button, dimmer, blind and thermostat functions ; with valve protection function ; button help function can be activated |
| Timers | with room temperature timer and 2-week timer functions |
| Operating mode | controller operating modes: comfort, standby, night and frost/heat protection mode |

Compatibility

| | |
|----------------|--|
| Extension unit | extension unit for light scene push-button |
|----------------|--|

Controls and indicators

| | |
|----------------------|--|
| With LED indication | Yes |
| Dimming | area dimming |
| Number of buttons | 4 |
| Operation | one push-button operation for switching, pushing, shutters and dimming ; blind operating concepts short-long-short and long-short parameterisable |
| Indication / display | display of operating mode, controller lockout, room/outside temperature, time (clock required) ; LC display with symbols and illumination, switchable via object |
| Button / push-button | with 2 additional display buttons |

Connectivity

| | |
|----------|-------------------------------|
| Encoding | with button blocking function |
|----------|-------------------------------|

Dimensions

| | |
|------------------------------------|-----------|
| Assembling height | 16.7 mm |
| Width of rail mounted device (RMD) | 0 modules |
| Height | 149.2 mm |
| Width | 88.5 mm |

Measurement

| | |
|-------------------|---|
| Value transmitter | value transmitter for dimming, position, brightness and temperature values 1 and 2 byte |
|-------------------|---|

Screen

| | |
|--------------|-----|
| With display | Yes |
|--------------|-----|

Materials

| | |
|------------------------|---------------------|
| Colour of design line | Aluminium |
| Material / workmanship | aluminium, anodised |

| | |
|--|--|
| Surface appearance | matt |
| Material family | Metal |
| LED control | |
| LED | with blue operation LED and 8 white status LEDs (labelling field illumination) |
| Connection | |
| Bus coupling unit | For flush-mounted bus coupling unit for B.IQ with thermostat |
| Settings | |
| Parameterisation | single and two push-button operation parameterisable ; end customer display scope parameterisable ; presence button parameterisable to extend comfort |
| Programming | programmable from ETS2, V1.2a |
| Accessories included | |
| Box | for installation in single standard wall boxes |
| Matching products | for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for aluminium frames in the same "style" for additional applications, see the Design line B.7 |
| Equipment | |
| Number of actuation points | 10 |
| Product type: | product type: B.IQ |
| Heating | for heating and/or cooling mode with/without auxiliary step |
| Control | control parameter for heating / cooling unit pre-set ; for individual single room temperature control ; for continuous (PI) or switched (2-point) control of max. 2 control circuits |
| Use | |
| Differentiation characteristic 2 - Sales | Display |
| Software | |
| Update | with flash-controller technology |
| Safety | |
| Protection | with dismantling protection |
| Alarm | alarm telegram after disconnection from bus coupling unit 1 bit, 1 or 2 byte |
| Use conditions | |
| Operating temperature | -5...45 °C |
| Temperature | provision of the internal temperature value via communication object ; temperature measurement via internal temperature sensor and/or external communication object (weighting ratio parameterisable) |
| Energy efficiency class | IV (2%) |
| Identification | |
| Application, usage | KNX - operating systems |

| | |
|--------------------------|-----------------------------|
| Product family | product family: push-button |
| Release issue | 2.6 |
| Main design line | KNX - Berker B.IQ |
| Secondary design line(s) | KNX ; Berker B.IQ |