



75664594



## B.IQ push-button 4gang thermostat, display, KNX - B.IQ, al., al. anodised

### Technical characteristics

#### Functions

With room temperature controller	Yes
Function	for switch, push-button, dimmer, blind and thermostat functions, with valve protection function, button help function can be activated
Timers	with room temperature timer and 2-week timer functions
Operating mode	controller operating modes: comfort, standby, night and frost/heat protection mode

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Dimming	area dimming
Number of buttons	4
Operation	one push-button operation for switching, pushing, shutters and dimming, blind operating concepts short-long-short and long-short parameterisable
Indication / display	display of operating mode, controller lockout, room/outside temperature, time (clock required), LC display with symbols and illumination, switchable via object
Button / push-button	with 2 additional display buttons

#### Connectivity

Encoding	with button blocking function
----------	-------------------------------

#### Dimensions

Assembling height	16.7 mm
Width of rail mounted device (RMD)	0 modules
Height	149.2 mm
Width	88.5 mm

#### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

#### Screen

With display	Yes
--------------	-----

#### Materials

Colour of design line	Aluminium
RAL colour	RAL 9006 - White aluminium

Material / workmanship	aluminium, anodised
Material	Aluminium
Surface appearance	matt
Material family	Metal
<b>LED control</b>	
LED	with blue operation LED and 8 white status LEDs (labelling field illumination)
<b>Connection</b>	
Bus coupling unit	For flush-mounted bus coupling unit for B.IQ with thermostat
<b>Settings</b>	
Parameterisation	single and two push-button operation parameterisable, end customer display scope parameterisable, presence button parameterisable to extend comfort
Programming	programmable from ETS2, V1.2a
<b>Accessories included</b>	
Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for aluminium frames in the same "style" for additional applications, see the Design line B.7
<b>Equipment</b>	
Number of actuation points	10
Product type:	product type: B.IQ
Heating	for heating and/or cooling mode with/without auxiliary step
Control	control parameter for heating / cooling unit pre-set, for individual single room temperature control, for continuous (PI) or switched (2-point) control of max. 2 control circuits
<b>Use</b>	
Differentiation characteristic 2 - Sales	Display
<b>Software</b>	
Update	with flash-controller technology
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit, 1 or 2 byte
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Temperature	provision of the internal temperature value via communication object, temperature measurement via internal temperature sensor and/or external communication object (weighting ratio parameterisable)

Subject to technical modifications

**Identification**

Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX, Berker B.IQ