



75141326



IP20



Technical characteristics

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Light scenes retrieval, adjustment and storage of 8 light scenes

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 1

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 56.4 mm

Height 71 mm

Width 71 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of labelling 217,217,217

Colour of design line anthracite

Material for printing Paper

Surface appearance velvety

Type of surface treatment untreated

Material family Plastic

LED control

LED with white operation LED and 2 amber status LEDs

Settings

Supported configuration modes system

Parameterisation single and two push-button operation parameterisable

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of actuation points	2
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 1gang
Controller extension unit	usable as thermostat extension unit

Use

Differentiation characteristic 1 - Sales	with labelling field
Differentiation characteristic 3 - Sales	with integral bus coupling unit

Safety

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions

Information text	Labelling field sheet, order no. 9498 29 01, available separately.
------------------	--