




75664690

IP20



## B.IQ IR Push Button with Thermostat, 4-Gang, Glass Polar White

### Technical characteristics

#### Functions

Function with valve protection function

Timers with room temperature timer and 2-week timer functions

#### Compatibility

Extension unit extension unit for light scene push-button

#### Controls and indicators

Number of buttons 4

Operation one push-button operation for switching, pushing, shutters and dimming

#### Dimensions

Width of rail mounted device (RMD) 0 modules

Height 158.2 mm

Width 88.5 mm

#### Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

#### Materials

Colour of design line glass polar white

RAL colour RAL 9010 - Pure white

Material glass

#### LED control

LED with blue operation LED and 8 white status LEDs (labelling field illumination)

#### Settings

Parameterisation single and two push-button operation parameterisable

#### Accessories included

Box for installation in single standard wall boxes

Matching products for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for glass frames in the same "style" for additional applications, see the Design line B.7

#### Equipment

Product type: product type: B.IQ

Control for individual single room temperature control

---

**Software**

Update with flash-controller technology

---

**Safety**

Protection with dismantling protection

---

**Use conditions**

Operating temperature -5...45 °C

Energy efficiency class IV (2%)

---

**Identification**

Application, usage KNX - operating systems

Product family product family: push-button

Release issue 2.6

Main design line KNX - Berker B.IQ

Secondary design line(s) Berker B.IQ, KNX

---

**Instructions**

Information text IR hand-held transmitter, order no. 2779