




75142034

IP20



KNX glass sensor 2gang comf, intg bus coupling unit, KNX - TS sensor, glass al.

Technical characteristics

Functions

With room temperature controller	Yes
Function	for switch, push-button, dimmer and shutter functions ; Blocking function for sensor surface e.g. for cleaning the glass surface

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	0
Operation	operation by gently touching the sensor surfaces on the white LED

Dimensions

Depth	37.7 mm
Depth	5.7 mm
Dimensions (W x H x D)	86 x 160 x 5.7 mm
Height	160 mm
Width	86 mm

Power

Current consumption	12.5 mA
---------------------	---------

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	No
--------------	----

Materials

Colour of design line	glass aluminium
Surface appearance	glossy/matt

LED control

LED	with blue operation LED and 4 white status LEDs
-----	---

Installation, mounting

Installation mode	for vertical mounting
-------------------	-----------------------

Connection

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Accessories included

Matching products	for glass frames in the same "style" for additional applications, see the Design line B.7 ; for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x
-------------------	--

Equipment

Number of actuation points	4
----------------------------	---

With anti-theft/dismantling protection	Yes
--	-----

Use

Differentiation characteristic 3 - Sales	with integral bus coupling unit
--	---------------------------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Temperature	temperature measurement via internal temperature sensor or external communication object ; integrated temperature sensor for operation as controller extension unit ; additional connection for external temperature sensor
-------------	---

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Main design line	KNX - Berker TS Sensor
------------------	------------------------

Secondary design line(s)	KNX ; Berker TS Sensor
--------------------------	------------------------

Instructions

Information text	Only suitable for KNX.
------------------	------------------------