



75665594



## B.IQ push-button 5gang thermostat, display, KNX - B.IQ, al., al. anodised

### Technical characteristics

#### Functions

With room temperature controller	Yes
Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

#### Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

#### Controls and indicators

With LED indication	Yes
Number of buttons	5
Operation	one push-button operation for switching, pushing, shutters and dimming

#### Dimensions

Assembling height	16.7 mm
Width of rail mounted device (RMD)	0 modules
Height	178.8 mm
Width	88.5 mm

#### Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

#### Screen

With display	Yes
--------------	-----

#### Materials

Colour of design line	Aluminium
RAL colour	RAL 9006 - White aluminium
Material / workmanship	aluminium, anodised
Material	Aluminium
Material family	Metal

#### Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

#### Scope of delivery

Bus connection included	No
-------------------------	----

#### Accessories included

Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for aluminium frames in the same "style" for additional applications, see the Design line B.7
<b>Equipment</b>	
Product type:	product type: B.IQ
Control	for individual single room temperature control
<b>Software</b>	
Update	with flash-controller technology
<b>Safety</b>	
Protection	with dismantling protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)
<b>Identification</b>	
Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ, KNX