


75144329



Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Light scenes retrieval, adjustment and storage of 8 light scenes

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 4

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 56.4 x 12 mm

Height 71 mm

Width 71 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of design line polar white

Colour polarwhite

RAL colour RAL 9010 - Pure white

Material Plastic/metal

Material for printing Paper

Surface appearance velvety

Type of surface treatment untreated

Material family Plastic

LED control

LED with white operation LED and 8 amber status LEDs

Settings	
Supported configuration modes	system
Parameterisation	single and two push-button operation parameterisable
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of actuation points	8
With anti-theft/dismantling protection	Yes
Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 4gang
Controller extension unit	usable as thermostat extension unit
Use	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with integral bus coupling unit
Safety	
Protection index IP	IP20
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Main design line	KNX - Berker Q.1/Q.3
Secondary design line(s)	Berker Q.3, Berker Q.7, Berker Q.1
Instructions	
Information text	Labelling field sheet, order no. 9498 32 04, available separately.