



75161093

IP20

B.IQ push-button 1gang, KNX - B.IQ, stainless steel, metal brushed

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 1

Dimensions

Assembling height 16.7 mm

Height 88.5 mm

Width 88.5 mm

Measurement

Value transmitter dimming / position value transmitter 1 byte

Screen

With display No

Materials

Colour of design line Stainless steel

Colour stainless steel

RAL colour RAL 9022 - Pearl light grey

Material / workmanship metal brushed

Material stainless steel

Surface appearance matt

Type of surface treatment brushed

LED control

LED with blue operation LED and 2 white status LEDs (labelling field illumination)

Connection

Bus coupling unit for bus coupling unit flush-mounted

Scope of delivery

| | |
|-------------------------|----|
| Bus connection included | No |
|-------------------------|----|

Accessories included

| | |
|-----|--|
| Box | for installation in single standard wall boxes |
|-----|--|

Matching products

for stainless steel frames in the same "style" for additional applications, see the Design line B.7, for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x

Equipment

| | |
|----------------------------|---|
| Number of actuation points | 2 |
|----------------------------|---|

| | |
|--|-----|
| With anti-theft/dismantling protection | Yes |
|--|-----|

| | |
|---------------|--------------------|
| Product type: | product type: B.IQ |
|---------------|--------------------|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

| | |
|------------|-----------------------------|
| Protection | with dismantling protection |
|------------|-----------------------------|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

Identification

| | |
|--------------------|-------------------------|
| Application, usage | KNX - operating systems |
|--------------------|-------------------------|

| | |
|----------------|-----------------------------|
| Product family | product family: push-button |
|----------------|-----------------------------|

| | |
|------------------|-------------------|
| Main design line | KNX - Berker B.IQ |
|------------------|-------------------|

| | |
|--------------------------|------------------|
| Secondary design line(s) | Berker B.IQ, KNX |
|--------------------------|------------------|