



75162599



IP20

B.IQ push-button 2gang comf, KNX - B.IQ, p. white, matt, plastic

Technical characteristics

Functions

With room temperature controller No

Function for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 2

Operation activation of second user level via object ; one push-button operation for switching, pushing, shutters and dimming

Dimensions

Height 88.5 mm

Width 88.5 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display No

Materials

Colour of labelling 105,105,105

Colour of design line polar white

RAL colour RAL 9010 - Pure white

Surface appearance matt

Type of surface treatment untreated

LED control

LED with blue operation LED and 4 white status LEDs (labelling field illumination)

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Supported configuration modes system, PB

Parameterisation single and two push-button operation parameterisable

Scope of delivery

| | |
|-------------------------|----|
| Bus connection included | No |
|-------------------------|----|

Accessories included

| | |
|-----|--|
| Box | for installation in single standard wall boxes |
|-----|--|

| | |
|-------------------|--|
| Matching products | for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for plastic frames in the same "style" for additional applications, see the Design line B.7 |
|-------------------|--|

Equipment

| | |
|----------------------------|---|
| Number of actuation points | 4 |
|----------------------------|---|

| | |
|--|-----|
| With anti-theft/dismantling protection | Yes |
|--|-----|

| | |
|-----------------------|------------|
| Type of configuration | Laserdruck |
|-----------------------|------------|

| | |
|---------------|--------------------|
| Product type: | product type: B.IQ |
|---------------|--------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
|---------------|-----|

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|

| | |
|------------|-----------------------------|
| Protection | with dismantling protection |
|------------|-----------------------------|

| | |
|-------|---|
| Alarm | alarm telegram after disconnection from bus coupling unit 1 bit or 1 byte |
|-------|---|

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

Identification

| | |
|--------------------|-------------------------|
| Application, usage | KNX - operating systems |
|--------------------|-------------------------|

| | |
|----------------|-----------------------------|
| Product family | product family: push-button |
|----------------|-----------------------------|

| | |
|------------------|-------------------|
| Main design line | KNX - Berker B.IQ |
|------------------|-------------------|

| | |
|--------------------------|-------------------|
| Secondary design line(s) | KNX ; Berker B.IQ |
|--------------------------|-------------------|