



75163373



IP20



Technical characteristics

Functions

With room temperature controller	No
Function	for switch, push-button, dimmer and shutter functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--------------------------------------------

Controls and indicators

With LED indication	Yes
Number of buttons	3

Dimensions

Labelling field length (W x H)	66.8 x 15.7 mm
Height	55.1 mm
Width	70.5 mm

Measurement

Value transmitter	dimming / position value transmitter 1 byte
-------------------	---------------------------------------------

Screen

With display	No
--------------	----

Materials

Colour of labelling	105,105,105
Colour of design line	stainless steel
Material for printing	Paper
Surface appearance	matt
Material family	Plastic

LED control

LED - KNX	with white operation LED and 6 red status LEDs
-----------	------------------------------------------------

Connection

Bus coupling unit	for bus coupling unit flush-mounted
-------------------	-------------------------------------

Scope of delivery

Bus connection included	No
-------------------------	----

Equipment

Number of actuation points	6
With anti-theft/dismantling protection	Yes

Type of configuration	Beschriftungsfeld(er) - Folie
Product type:	product type: push-button 3gang
Use	
Differentiation characteristic 1 - Sales	with labelling fields
Differentiation characteristic 3 - Sales	with horizontal operation
Safety	
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Secondary design line(s)	KNX ; Berker K.5