



75441226



**KNX object thermostat, intg bus coupling unit, KNX, Q.x, ant. velvety, lacq.**

**Technical characteristics**

**Architecture**

Fixing mode flush-mounting

**Functions**

Operating mode operating modes: comfort, standby, night lowering, frost/heat protected, dewpoint

**Controls and indicators**

Button / push-button with programming button and red programming LED

**Connectivity**

Binary inputs with 4 independent binary inputs for potential-free contacts e.g. window magnetic contact ; 4 binary inputs or 2-3 binary inputs and 1-2 outputs parameterisable

**Voltage**

Operating voltage over bus 21...32 V DC

**Electric current**

Bus current consumption (data transfer) max. 7.5 mA

Output current per channel max. 0.8 mA

**Materials**

Colour of design line anthracite

RAL colour RAL 7021 - Black grey

Material / workmanship lacquered

Material Plastic/metal

Surface appearance velvety

Type of surface treatment Painted

**Installation, mounting**

Installation mode without spreader claws

**Connection**

Sensor cable length 50 m

Conductor cross-section (flexible) 0.3...1 mm<sup>2</sup>

Conductor cross-section (rigid) 1.5 mm<sup>2</sup>

Type of connection Binary inputs / outputs with screw terminals

Bus connection bus connection via connecting terminal

**Cable**

Cable length, inputs/outputs max. 5 m

**Settings**

---

Supported configuration modes	system
-------------------------------	--------

---

Parameterisation	conduct can be defined for bus voltage return ; valve protection can be defined
------------------	---

**Equipment**

---

Product type:	product type: thermostat
---------------	--------------------------

---

Heating	for heating and/or cooling mode ; heating or cooling possible in 2 stages
---------	---

---

Control	for continuous (PI) or switched (2-point) control ; for single room control
---------	---

**Use**

---

Differentiation characteristic 3 - Sales	with integral bus coupling unit
--	---------------------------------

**Safety**

---

Protection	with dismantling protection
------------	-----------------------------

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Energy efficiency class	IV (2%)
-------------------------	---------

**Identification**

---

Application, usage	KNX - sensors
--------------------	---------------

---

Product family	Product family: heating, ventilation, air conditioning
----------------	--

---

Main design line	KNX - Berker Q.1/Q.3
------------------	----------------------

---

Secondary design line(s)	KNX ; Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9
--------------------------	---

**Instructions**

---

Special note text	Binary input 4 parameter defineable for temperature sensor, order no. 161.
-------------------	--