


80960283

IP20



Cover for 1gang for push-button module, clearlens, S.1/B.3/B.7, al., matt, lacq.

Technical characteristics

Functions

operating concept "independent push-button" function predefined ; operating concept for "roller shutter/blind" function predefined ; switching of scenes (1..8) possible ; brightness value of the status LED for day/nighttime operation preset, change-over for day/nighttime operation possible ; integrated temperature sensor with output of the measured values ; Colour of status LED uniformly adjustable for complete device ; push-button functions: including switching, dimming, roller shutter/blind, timer, priority, operating mode changeover

Easy link functions

Function Function for manual interruption of automatic functions already triggered

Function operating surfaces as buttons (single-surface operation) and rockers (two-surface operation) ; the brightness of status LEDs are individually adjustable for button/ rocker function ; brightness value of the status LEDs for day/nighttime operation adjustable via object or manually ; value transmitter for dimming, position, brightness temperature values 1 and 2 byte ; integrated temperature sensor with output of the measured values via object ; parameter defineable lock function ; button/rocker functions for switching, dimming, roller shutter/blind, value transmitter 1/2 byte, room thermostat extension unit, priority, scene, automatic control deactivation

Controls and indicators

Operation operating areas configurable as one or two-area operation

Button / push-button with programming button and red programming LED

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Height 55 mm

Power

Power consumption, KNX ≈ 108 mW

Camera

Lens with clear lens for RGB status display of the push-button module

Materials

Colour of design line aluminium

Surface appearance matt

Connection

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

Settings

Supported configuration modes	system, easy
-------------------------------	--------------

Equipment

Buzzer/siren	with integrated buzzer for acoustic identification of the device within the system
--------------	--

Use

Differentiation characteristic 2 - Sales	with clear lens
--	-----------------

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Protection	with dismantling protection
------------	-----------------------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Temperature	integrated temperature sensor with output of the measured values via object
-------------	---

Identification

Application, usage	KNX - operating systems
--------------------	-------------------------

Product family	product family: push-button
----------------	-----------------------------

Main design line	KNX - Berker S.1/B.3/B.7
------------------	--------------------------

Secondary design line(s)	KNX ; Berker S.1 ; Berker B.3 ; Berker B.7
--------------------------	--