



75663591

Technical characteristics

Functions

With room temperature controller	Yes
Function	for switch, push-button, dimmer, blind and thermostat functions ; button help function can be activated ; with valve protection function
Timers	with room temperature timer and 2-week timer functions
Operating mode	controller operating modes: comfort, standby, night and frost/heat protection mode

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Dimming	area dimming
Number of buttons	3
Operation	one push-button operation for switching, pushing, shutters and dimming ; blind operating concepts short-long-short and long-short parameterisable
Indication / display	display of operating mode, controller lockout, room/outside temperature, time (clock required) ; LC display with symbols and illumination, switchable via object
Button / push-button	with 2 additional display buttons

Connectivity

Encoding	with button blocking function
----------	-------------------------------

Dimensions

Width of rail mounted device (RMD)	0 modules
Height	119.6 mm
Width	88.5 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Materials

Colour of design line	glass polar white
RAL colour	RAL 9010 - Pure white
Material family	Glass

LED control

LED	with blue operation LED and 6 white status LEDs (labelling field illumination)
-----	--

Connection

Bus coupling unit	For flush-mounted bus coupling unit for B.IQ with thermostat
-------------------	--

Settings

Parameterisation	presence button parameterisable to extend comfort ; end customer display scope parameterisable ; single and two push-button operation parameterisable
Programming	programmable from ETS2, V1.2a

Accessories included

Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x ; for glass frames in the same "style" for additional applications, see the Design line B.7

Equipment

Product type:	product type: B.IQ
Heating	for heating and/or cooling mode with/without auxiliary step
Control	for continuous (PI) or switched (2-point) control of max. 2 control circuits ; for individual single room temperature control ; control parameter for heating / cooling unit pre-set

Use

Differentiation characteristic 2 - Sales	Display
--	---------

Software

Update	with flash-controller technology
--------	----------------------------------

Safety

Protection	with dismantling protection
Alarm	alarm telegram after disconnection from bus coupling unit 1 bit, 1 or 2 byte

Use conditions

Operating temperature	-5...45 °C
Temperature	temperature measurement via internal temperature sensor and/or external communication object (weighting ratio parameterisable) ; provision of the internal temperature value via communication object
Energy efficiency class	IV (2%)

Identification

Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	KNX ; Berker B.IQ