



85020100



IP20

## Power supply for KNX radio application module, KNX Radio

### Technical characteristics

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Dimensions

Insertion depth	22 mm
-----------------	-------

Claw guidance installation depth	32 mm
----------------------------------	-------

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

Housing installation depth	22 mm
----------------------------	-------

#### Materials

Material	Plastic/metal
----------	---------------

#### Installation, mounting

Installation mode	with spreader claws
-------------------	---------------------

#### Connection

Number of contacts	1
--------------------	---

Type of connection	with screw terminals
--------------------	----------------------

#### Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Relative humidity (without condensation)	0...65 %
--	----------

#### Identification

Application, usage	KNX radio- operating systems
--------------------	------------------------------

#### Instructions

Special note text

Motion detector application modules in conjunction with a network insert can only be used as a motion detector extension unit (slave). For this purpose, a motion detector application module with a relay insert must be installed as a motion detector main unit (master) (order no.: 8512 12 00).