



85121100

**Switch insert 1gang, electronics**

**Technical characteristics**

**Functions**

Soft startup bulb-preserving soft startup

**Main electrical features**

Frequency 50/60 Hz

**Voltage**

Operating voltage 230 V AC

**Fuse**

Fuse short-circuit and overload proof (electronic fuse)

**Dimensions**

Insertion depth 32 mm

**Power**

Dimmable conventional transformers 25...400 VA

Power consumption, standby (Channel 1/Channel 2) < 0.3/0.7 W

Power consumption (standby) < 0.3 W

Electronic transformers and dual-mode transformers 25...400 W

**Measurement**

Extension unit input with extension unit input for push-button (NO contact), single-surface operation and motion detector extension unit

**Materials**

Material / surface no conductive connection between supporting ring and spreading claws

**Fluorescent bulbs control**

Dimmable energy-saving lamps 13...80 W

**LED control**

Dimmable 230 V retrofit LED lamps 5...70 W

**Incandescent bulbs control**

230 V incandescent lamps and halogen lamps 25...400 W

**Installation, mounting**

Installation mode with spreader claws

**Connection**

Screw terminals (max.)	2 x 1,5/1 x 2,5 mm <sup>2</sup>
Type of connection	with screw terminals
Number of substations	unlimited

**Cable**

Load cable length	max. 100 m
Cable length, extensions	max. 50 m

**Settings**

Setting	Optimisation of the dimming performance by fine adjustment of the load type and special adjustment mode
---------	---

**Equipment**

Dimming principle	automatic setting of load-dependent switching principle (autoDetect process)
-------------------	--

**Use conditions**

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

**Identification**

Application, usage	Light control ; Motion detector ; KNX radio- operating systems
Main design line	Electronics platform

**Instructions**

Special note text	Caution! Only connect dimmable 230 V ESL or retrofit-LED lamps.
Information text	Only suitable for operation with dimmable loads!