



85121100

Switch insert 1gang, electronics

Technical characteristics

Functions

Soft startup bulb-preserving soft startup

Main electrical features

Frequency 50/60 Hz

Voltage

Operating voltage 230 V AC

Fuse

Fuse short-circuit and overload proof (electronic fuse)

Dimensions

Insertion depth 32 mm

Power

Dimmable conventional transformers 25...400 VA

Power consumption, standby (Channel 1/Channel 2) < 0.3/0.7 W

Power consumption (standby) < 0.3 W

Electronic transformers and dual-mode transformers 25...400 W

Materials

Material Plastic/metal

Fluorescent bulbs control

Dimmable energy-saving lamps 13...80 W

LED control

Dimmable 230 V retrofit LED lamps 5...70 W

Incandescent bulbs control

230 V incandescent lamps and halogen lamps 25...400 W

Installation, mounting

Installation mode with spreader claws

Connection

Type of connection with screw terminals

Number of substations unlimited

Cable

Load cable length	max. 100 m
Cable length, extensions	max. 50 m
Use conditions	
Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)
Identification	
Application, usage	Light control, Motion detector, KNX radio- operating systems
Instructions	
Special note text	Caution! Only connect dimmable 230 V ESL or retrofit-LED lamps.
Information text	Only suitable for operation with dimmable loads!