



75665593



B.IQ push-b. 5gang thermostat, display, KNX - B.IQ, stainl. steel metal brushed

Technical characteristics

Functions

With room temperature controller	Yes
Function	with valve protection function
Timers	with room temperature timer and 2-week timer functions

Compatibility

Extension unit	extension unit for light scene push-button
----------------	--

Controls and indicators

With LED indication	Yes
Number of buttons	5
Operation	one push-button operation for switching, pushing, shutters and dimming

Dimensions

Assembling height	16.7 mm
Width of rail mounted device (RMD)	0 modules
Height	178.8 mm
Width	88.5 mm

Measurement

Value transmitter	value transmitter for dimming, position, brightness and temperature values 1 and 2 byte
-------------------	---

Screen

With display	Yes
--------------	-----

Materials

Colour of design line	Stainless steel
RAL colour	RAL 9022 - Pearl light grey
Material / workmanship	metal brushed
Material	stainless steel
Material family	Metal

Settings

Parameterisation	single and two push-button operation parameterisable
------------------	--

Scope of delivery

Bus connection included	No
-------------------------	----

Accessories included

Box	for installation in single standard wall boxes
Matching products	for additional products to complement the installation in matching colours/materials, refer to the Design platform S.1/B.x, for stainless steel frames in the same "style" for additional applications, see the Design line B.7
Equipment	
Product type:	product type: B.IQ
Control	for individual single room temperature control
Software	
Update	with flash-controller technology
Safety	
Protection	with dismantling protection
Use conditions	
Operating temperature	-5...45 °C
Energy efficiency class	IV (2%)
Identification	
Application, usage	KNX - operating systems
Product family	product family: push-button
Release issue	2.6
Main design line	KNX - Berker B.IQ
Secondary design line(s)	Berker B.IQ, KNX