



85146131



IP20

KNX radio button 2gang quicklink, R.1/R.3/1930/R.cl., black glossy

Technical characteristics

Functions

ETS additional functions	ETS additional functions: +6 scenes, 1 button control up/down, operating mode on/off, dimming value, brightness display, push-button, status display, forced control
Quicklink functions	quicklink functions: switching, dimming, blind, 2 scenes, time switching, NO contact push-button, memory

Connectivity

Radio protocol	KNX Radio
Receiver category	2

Power

Radio transmission power	< 10 mW
--------------------------	---------

Materials

Colour of labelling	217,217,217
Colour of design line	black
RAL colour	RAL 9005 - Jet black
Material	thermoplastic
Material for printing	PC-PMA black

Equipment

Number of radio channels	4
Number of quicklink links	max. 20 transmitter/receiver
Type of configuration	Laserdruck
Transmitter duty cycle	1 %

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Light control, KNX radio- operating systems
Main design line	Berker R.1/R.3/R.8/Serie 1930/R.classic

Instructions

Special note text

Note: When integrating this product into the Serie 1930, the 1gang frame for centre plate Ø 58 mm, order no.: 1382 0... may only be used. Installation in multiple combinations of the Serie 1930 is not possible!