



75665780



Push-button, 5-gang, with room thermost

Technical characteristics

Architecture

Fixing mode flush-mounting

Functions

With room temperature controller Yes

Function with valve protection function

Timers with room temperature timer

Compatibility

Extension unit extension unit for light scene push-button

Controls and indicators

With LED indication Yes

Number of buttons 5

Operation one push-button operation for switching, pushing, shutters and dimming

Dimensions

Labelling field length (W x H) 52.3 x 15.6 mm

Height 111 mm

Width 55.8 mm

Measurement

Value transmitter value transmitter for dimming, position, brightness and temperature values 1 and 2 byte

Screen

With display Yes

Materials

Colour independent of design lines for white and polar white

Colour other

RAL colour RAL 1013 - Oyster white

Material thermoplastic

Material for printing Paper

Type of surface treatment untreated

Connection

Bus coupling unit for bus coupling unit flush-mounted

Settings

Parameterisation

single and two push-button operation
parameterisable

Scope of delivery

Bus connection included No

Equipment

Number of actuation points 12

With anti-theft/dismantling protection Yes

Type of configuration Beschriftungsfeld(er) - Folie

Control for individual single room temperature control

Software

Update with flash-controller technology

Safety

Protection index IP IP20

Protection with dismantling protection

Alarm alarm telegram after disconnection from bus
coupling unit 1 bit or 1 byte

Use conditions

Operating temperature -5...45 °C

Energy efficiency class IV (2%)

Identification

Application, usage KNX - operating systems

Product family product family: push-button

Main design line KNX - Berker S.1/B.3/B.7

Secondary design line(s) KNX, Berker S.1, Berker B.3, Berker B.7

Instructions

Special note text Use only in combination with frame frame with large
cut-out.