



85241124

Blind button Q.x alu velvety, lacquered

Technical characteristics

Functions

Venetian blind movement time 2 mn

Function Memory function for automatic execution of learned up and down times with position ; Party function, no execution of automatic, radio and extension unit commands (lock-out protection)

Controls and indicators

Operation activation of the party function using buttons in up and down direction > 20 sec.

Main electrical features

Nominal voltage 12 V

Frequency - Hz

Detection

Sensor Not suitable for rain and wind sensors

Materials

Colour of design line aluminium

Material / workmanship lacquered

LED control

LED LED application module/insert compatibility display ; with status LED for memory and party function, red/orange ; with indicator LED for lock-out protection

Installation, mounting

Installation mode clamp fastening

Settings

Lamella adjusting time (adjustable) 50 ms...2.5 s

Minimum slat adjustment time ≈ 250 ms

Delay time, adjustable 0...500 s

Lamella adjustment on button-press < 0.4 s

Equipment

Self-retaining for 2 min on button-press > 0.4 s

Change-over time for change of direction < 0.6 s

Safety

Halogen free No

Protection with dismantling protection

Use conditions

Operating temperature	-5...45 °C
Energy-saving	low intrinsic energy requirement
Relative humidity (without condensation)	0...65 % (without condensation)

Identification

Application, usage	Blind control
Main design line	Berker Q.1/Q.3/Q.7/Q.9
Secondary design line(s)	Berker Q.1 ; Berker Q.3 ; Berker Q.7 ; Berker Q.9

Instructions

Special note text	Can be switched to orientation led by extension unit.
-------------------	---
