



75740012

Technical characteristics

Functions

Timers	time switch (weekly) with 16 channels each with 8 switching times
--------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Auxiliary voltage	230 V AC
Operating voltage over bus	21...32 V DC

Dimensions

Depth	46 mm
Height	141 mm
Width	221 mm

Measurement

Limit values	max. 32
--------------	---------

Screen

Resolution graphical display	320 x 240 / 240 x 320 px
TFT screen size	5.7 "

Storage

Graphics memory	≈ 4 MB
-----------------	--------

Materials

Colour of design line	polar white
RAL colour	RAL 9010 - Pure white
Material	Aluminium

Connection

Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal

Equipment

Clock	with synchronisable integral real-time clock with date
-------	--

Use conditions

Operating temperature	-5...45 °C
Logic operations (cascadable)	80

Identification	
Application, usage	KNX - operating systems
Main design line	KNX